

# ADAPTER SINGLEMODE - SC/SC METAL

Product sheet  
Adapter single mode - SC/  
SC Metal

V1.0, 2022-03-10

Micropol Fiberoptic AB  
Älvdalsvägen 4  
313 50 Åled

Phone: +46 (0)35 17 85 39  
Mail: info@micropol.com

Adapter is used to connect two opto contacts. In the adapter you find a alignment sleeve lining up the ferrules and connecting the fiber cores.

For best performance you need ceramic alignment sleeves in the single mode adapters.



## SC/SC

Adapter SC Duplex in metal with ceramic alignment sleeve in Zirconia/  
Zirconium (Zr)

Simplex- and duplex version

Screw or- and snap mount

Color : silver

## SPECIFICATION

Variation in attenuation < 0,2  
dB

Life span	500 matings
Temperature	-40 — +85 °C
Vibrations	10-55 Hz (2h)
Fall test	1,5 m (8 times)

## Measurements

Hole image panel Simplex	9,9 x 13,3 mm
Hole image panel Duplex	9,9 x 26,4 mm

Article number	E-number	Description	Pack
85335-005	—	Adapter-SM-SC/SC-DPLX-Zr-Sn/FI-Metal	pce